

LOW VOLTAGE





Gel: UL 94-HB

Ray

Tech

Dielectric strength: >20 kV/mm Cross linking time: fast (about 15 min. at 25°C) Volume resistivity: >2 . $10^{15} \Omega$ cm Operating temperature: - $60^{\circ}C / +200^{\circ}C$ Overload temperature for short periods: up to 250°C Stabilised for: mould - UV Decreto e for storetion:

Degree of protection: IP68 (in proper casings)

Magic Power Gel protects against dust and seals the connections from the effects of continuous immersion in water when it is poured into casings protected from the ingress of solid bodies, thus helping to create a **IP68** system.





MAGIC POWER GEL

The unique two component gel in a single bottle, with superior dielectric, sealing and thermal characteristics, re-enterable and re-usable!

ADVANTAGES

- Very sticky.
- Strong self amalgamating characteristics.
- ► The gel is not-classified as hazardous under the CLP Directive.
- Single compact bottle; convenient twin compartment.
- Re-usable as well as re-enterable, even after long working periods.
- It doesn't give any waste.
- No shelf life.





For all types of connections, even in the toughest conditions, for power, telecom and signalling!

FILLERS

CASTING APPLICATION















STICKINESS

- Exceptional sealing properties in any condition.
- Better resistance to pressure.
- Effective even in vertical
- or ceiling applications.

ZERO WASTE

- Due to the nature of the product waste is eliminated; even residual product can be saved and used for the next application.
- Also any left over product maintains its high performance characteristics.



- Once cross linked it perfectly adheres on itself to get an homogeneous and compact mass.
- It can be therefore applied in multiple layers.


SINGLE BOTTLE

- Highly useful.
- The most compact packaging.
- Less space occupied in the toolbox.
- Both components in the same packaging.

PRODUCT / Item	Colour	Package type	Quantity
MAGIC POWER GEL 250 MAGICPOWER-250	•	1 single, two-component bottle	250 ml
MAGIC POWER GEL 500 MAGICPOWER-500	•	1 single, two-component bottle 1 jug - 1 spatula in wood	500 ml
MAGIC POWER GEL MAGICPOWER-GEL	•	1 single, two-component bottle 1 jug - 1 spatula in wood	1000 ml



PRODUCT / Item	Colour	Package type	Quantity
MAGIC POWER GEL BAG 150 MAGICPOWERBAG150	•	Two-component single dose bag	150 ml
MAGIC POWER GEL BAG 250 MAGICPOWERBAG250	•	Two-component single dose bag	250 ml



AFTER CURING MANUAL APPLICATION CEILING or WALL application

